

M8 ADAPTOR ON TOP OF MSUD VALVE PLUG FORM BI 11MM

Without electronics 60 V AC/DC


Form BI (11 mm) – M8, connector top entry
 max. 60 V AC/DC
 without components
 3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Form

Form 88941

General data

Pollution Degree	3
Mounting method	inserted, tightened
Temperature range	-25...+85 °C

Technical Data

Operating voltage	max. 60 V AC/DC
Rated surge voltage	1.5 kV
Operating current per contact	max. 4 A
Configuration	2 contacts + PE
Material group	IEC 60664-1, category I
LED display	no
Locking of ports	M3/M8 (recommended torque 0.4 Nm)
Protection	IP67 inserted and tightened (EN 60529)
Locking material	Steel (galvanized)

Commercial data

country of origin	CZ
customs tariff number	85366990
EAN	4048879115902
eClass	27143423
Packaging unit	1