

M8 ADAPTOR ON REAR / MSUD VALVE PLUG FORM C 8MM

Form C (8 mm) – M8, connector at the rear

24 V AC $\pm 20\%$ / DC $\pm 25\%$

LED and suppressor diode

3-pole

Plastic housings with good resistance against chemicals and oils.

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form 88975

General data

Pollution Degree 3
 Mounting method inserted, tightened
 Temperature range -25...+85 °C

Technical Data

Operating voltage 24 V AC $\pm 20\%$ / DC $\pm 25\%$
 Rated surge voltage 0.8 kV
 Operating current per contact max. 4 A
 Configuration 2 contacts + bridged PE
 Material group IEC 60664-1, category I
 Switch off peak max. 55 V
 LED display yellow
 Locking of ports M3/M8 (recommended torque 0.4 Nm)
 Protection IP67 inserted and tightened (EN 60529)
 Locking material Steel (galvanized)

Commercial data

country of origin CZ
 customs tariff number 85366990
 EAN 4048879347433
 eClass 27143423
 Packaging unit 1

