

**MKDP 24/23**

Cable entry plate

Size 24

Cable diameter (23)× 4.1...8.1 mm

[Link to Product](#)**Illustration**

Product may differ from Image

**Form**

Form 90201

**General data**

Dimensions H×W×D 147.5×59.5×25 mm

Temperature range -30...+90 °C

**Technical Data**

Protection IP66

Material TPE

Housing Polyamide

Fire category/fire behavior (UL94): VO

Sealing range (cable Ø) Cable diameter (23)× 4.1...8.1 mm

**Commercial data**

country of origin DE

customs tariff number 39269097

EAN 4048879568586

eClass 27279221

Packaging unit 1