

MKDP 24/29

Cable entry plate

Size 24

Cable diameter (29)× 3...6.5 mm

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form 90201

General data

Dimensions H×W×D 147.5×59.5×25 mm

Temperature range -30...+90 °C

Technical Data

Protection IP66

Material TPE

Housing Polyamide

Fire category/fire behavior (UL94): VO

Sealing range (cable Ø) Cable diameter (29)× 3...6.5 mm

Commercial data

country of origin DE

customs tariff number 39269097

EAN 4048879568593

eClass 27279221

Packaging unit 1