

M12/D-SUB PROFIBUS ADAPTER 180°

M12 male B-cod. / M12 female B-cod.

PROFIBUS

Bus connection plug 180°

SUB-D9 (male); M12× 1 mm, B-coded

[Link to Product](#)**Illustration**

Product may differ from Image

Form

Form 99421

General data

Protection	IP30
Dimensions H×W×D	77×31×15 mm
Temperature range	-20...+70 °C

Technical Data

Operating voltage	4.75...5.25 V DC (via the fieldbus device)
Current consumption	max. 12.5 mA
Transfer rate	max. 12 Mbit/s
Connection	M12×1 mm
Terminating resistor	integrated, switchable

Commercial data

country of origin	HU
customs tariff number	85366990
EAN	4048879303644
eClass	27061801
Packaging unit	1