


**CABLE DRUM Ø 355MM**

PVC 3x0.25 black 100m

Cable drum (100 m)

PVC (UL/CSA)

3× 0.25 mm<sup>2</sup>, gray[Link to Product](#)**Illustration**

Product may differ from Image

**Cables**

|                                    |                                         |
|------------------------------------|-----------------------------------------|
| No./diameter of wires              | 3× 0.25 mm <sup>2</sup>                 |
| Wire isolation                     | PVC (br, bl, bk)                        |
| Material (jacket)                  | PVC (UL/CSA)                            |
| Outer Ø                            | 4.5 mm ±5%                              |
| Bend radius (moving)               | 10× outer Ø                             |
| Temperature range (fixed)          | -30...+80 °C                            |
| Temperature range (mobile)         | -5...+80 °C                             |
| Cable identification               | 610                                     |
| Cable Type                         | 1 (PVC)                                 |
| Approval (cable)                   | UL (AWM-Style 2464/1731), CSA           |
| Cable weight [g/m]                 | 29,37                                   |
| Material (wire)                    | Cu wire, bare                           |
| Resistor (core)                    | max. 79 Ω/km (20 °C)                    |
| Single wire Ø (core)               | 0.15 mm                                 |
| Construction (core)                | 14× 0.15 mm (multi-strand wire class 5) |
| Diameter (core)                    | 3× 0.25 mm <sup>2</sup>                 |
| AWG                                | similar to AWG 24                       |
| Material (wire isolation)          | PVC                                     |
| Material property (wire isolation) | CFC-, cadmium-, silicone- and lead-free |
| Shore hardness (wire isolation)    | 45 ±5 D                                 |
| Wire-Ø incl. isolation             | 1.25 mm ±5%                             |
| Color/numbering of wires           | br, bk, bl                              |
| Stranding combination              | 3 wires twisted                         |
| Shield                             | no                                      |

|                            |                                                |
|----------------------------|------------------------------------------------|
| Material (jacket)          | PVC                                            |
| Material property (jacket) | CFC-, cadmium-, silicone- and lead-free        |
| Shore hardness (jacket)    | 85 ±5 A                                        |
| Outer-Ø (jacket)           | 4.5 mm ±5%                                     |
| Color (jacket)             | black                                          |
| chemical resistance        | good resistance to oil, gasoline and chemicals |
| thermal resistance         | flame retardant UL 1581 VW1 / CSA FT1          |
| Nominal voltage            | UL 300 V AC                                    |
| Test voltage               | 2000 V AC                                      |
| Current load capacity      | to DIN VDE 0298-4                              |
| Temperature range (fixed)  | -30...+80 °C                                   |
| Temperature range (mobile) | -5...+80 °C                                    |
| Bend radius (fixed)        | 5× outer Ø                                     |
| Bend radius (moving)       | 10× outer Ø                                    |
| Jacket Color               | black                                          |

#### Commercial data

|                       |               |
|-----------------------|---------------|
| country of origin     | DE            |
| customs tariff number | 85444995      |
| EAN                   | 4048879414050 |
| eClass                | 27062011      |
| Packaging unit        | 1             |