

**cable drum Ø 355mm**

PUR 1.5 shielded or UL/CSA+drag ch. 100m

Cable drum (100 m)  
 PUR (UL/CSA)  
 Wire diameter 0.15 mm<sup>2</sup>  
 Suitable for robots  
 suitable for C-tracks  
 10 Mio.

**Link to Product**

Cables	
Cable number	821
No./diameter of wires	(4G1.5 + (2× 1.5)C)-C
Wire isolation	TPM (bk num, gnye)
C-track properties	10 Mio.
Torsion stress	±30 °/m
Jacket Color	orange
Material (jacket)	PUR (UL/CSA) (=MC800+)
Specification	6FX8008-1BA11
Outer Ø	11.6 mm ±5%
Bend radius (fixed)	5× outer Ø
Bend radius (moving)	7.5× outer Ø
Temperature range (fixed)	-50...+80 °C
Temperature range (mobile)	-35...+70 °C
Shield	yes
Approval (cable)	cURus (AWM-Style 21223/10492)
Diameter (core)	4× 2.5 + 2× 1.5 mm <sup>2</sup>
Commercial data	
country of origin	DE
customs tariff number	85444995
EAN	4048879671385
eClass	27062011
Packaging unit	1