

cable drum Ø 355mm

PVC 1.5 geschirmt or UL/CSA+schleppk. 100m

Cable drum (100 m)
 PVC (UL/CSA)
 Wire diameter 0.15 mm²
 Suitable for robots
 suitable for C-tracks
 0.1 Mio.

Link to Product

Cables	
Cable number	861
No./diameter of wires	(4G1.5 + (2× 1.5)C)-C
Wire isolation	TPM (bk num, gnye)
C-track properties	0.1 Mio.
Torsion stress	±30 °/m
Jacket Color	orange
Material (jacket)	PVC (UL/CSA) (=MC500)
Specification	6FX5008-1BA11
Outer Ø	10.4 mm ±5%
Bend radius (fixed)	5× outer Ø
Bend radius (moving)	18× outer Ø
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-20...+60 °C
Shield	yes
Approval (cable)	UL (AWM-Style 2570/10492), CSA
Diameter (core)	4× 2.5 + 2× 1.5 mm ²
Commercial data	
country of origin	IT
customs tariff number	85444995
EAN	4048879671262
eClass	27062011
Packaging unit	1