

M12 Power L-cod. 5pol. female recept. front mount

wires PUR 5x1.5 1m

Flange female

M12, 5-pole

L-coded

Front mounting



with multi-strand wire

The resistance to aggressive media should be individually tested for your application. Further details on request.

Further cable lengths on request.

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Form

Form P4291

General data

Standards	IEC 61076-2-111
Pollution Degree	3
Mounting set	Screw thread (M16×1.5 mm) mounting nut

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

Material (gasket)	FKM
-------------------	-----

Cables

Cable number	980
--------------	-----

No./diameter of wires	5 × 1.5 mm ²
-----------------------	-------------------------

Wire isolation	PUR (br, wh, bl, bk, gr)
----------------	--------------------------

Bend radius (fixed)	7.5 × outer Ø
---------------------	---------------

Temperature range (fixed)	-40...+90 °C
---------------------------	--------------

Temperature range (mobile)	-25...+90 °C
----------------------------	--------------

Shield	no
--------	----

Outer Ø	2.4 mm ±5%
---------	------------

Technical Data

Operating voltage	max. 63 V AC/DC
-------------------	-----------------

Rated surge voltage	1.5 kV
---------------------	--------

Operating current per contact	max. 16 A; max. 14 A (UL-Recognized)
-------------------------------	--------------------------------------

Material group	IEC 60664-1, category I
----------------	-------------------------

Coding	L-coded
--------	---------

Locking of ports	Screw thread (M12×1 mm) recommended torque 0.6 Nm, self-securing
------------------	--

Compression gland	Flange (SW17)
-------------------	---------------

Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
------------	--

Protection NEMA	3, 4, 6P (UL 50E)
-----------------	-------------------

Locking material	Brass, nickel plated
------------------	----------------------

suitable for corrugated tube (internal Ø)	without
---	---------

Housing	Brass, nickel plated
---------	----------------------

Commercial data

country of origin	DE
-------------------	----

customs tariff number	85444290
-----------------------	----------


EAN	4048879636247
-----	---------------

eClass	27279220
--------	----------

Packaging unit	1
----------------	---

Sketch

Female



Product may differ from Image