

B24 Bulkhead mounted h., IP65

Single locking lever m.

B24

Bulkhead mounted housing

Single locking lever

IP65

Technical data will be only guaranteed with Murrelektronik components.

[Link to Product](#)**Illustration**

Product may differ from Image

General data

Housing type	Bulkhead mounted housing
Size	B24
Dimensions H×W×D	28.5×43×140 mm
Material (housing)	Aluminum die-cast
Material (housing surface)	powder-coated
Locking material	Steel (galvanized)
Material (gasket)	NBR
Climatic category	40/100/21 (EN 60068-1)
Temperature range	-40...+100 °C

Technical Data

Locking of ports	Single locking lever
Protection (housing)	IP65 inserted and tightened (EN 60529)
Mating cycles	min. 500

Commercial data

country of origin	CZ
customs tariff number	85389099
EAN	4048879646789
eClass	27143424
Packaging unit	1