

**EXACT12, 8XM12, 5-POLE, CAP, PLUG. SPRING TERM.**

Self wireable, PNP LED

8-way, 5-pole

Form PNP

Spring clamp plug-in terminals

Plastic housings with good resistance against chemicals and oils.





The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration




M12-Females 5-pole



Product may differ from Image

### Approvals



### Contact Layout

PIN 1	(+)
PIN 2	(NC)/(S2)
PIN 3	(-)
PIN 4	(NO)/(S1)
PIN 5	(Earth)
LED display	LED (green): Power / LED (yellow): (S1) / LED (white): Signal (S2)

### General data

Temperature range	-20...+70 °C
-------------------	--------------


### Technical Data

Operating voltage	24 V DC
Operating current per contact	max. 4 A
Total current	max. 8 A
Connection	Spring clamp plug-in terminals: max. 1.5 mm <sup>2</sup> (AWG 16)
Protection	IP65/IP67
Housing	Plastic, flame retardant

### Commercial data

country of origin	DE
customs tariff number	85369010
EAN	4048879053853
eClass	27143423
Packaging unit	1

### Sketch



Product may differ from Image