

MICO+ 4.4 electronic circuit protection, 4 CHANNELS

IN: 24 V DC OUT: 24 V / 1-2-3-4 A

MICO+ 4.4
4 channels
Current adjustment 1, 2, 3, 4 A

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals**Input**

Operating voltage 24 V DC (18...30 V DC)

Output

Current adjustment 1 A, 2 A, 3 A, 4 A, by countersunk rotary switch, sealed

Inrush capacity max. 20 mF (per channel)

Control inputs

Input voltage (ON) 10...30 V DC

Remote start (OFF) 10...30 V DC

Impulse length (ON) min. 20 ms

Control outputs

Group alarm output max. 20 mA; high: all channels ON; low: not all channels ON

Early warning (90%) max. 20 mA; high: one channel over 90%; low: all channels under 90%

General data

Connection Spring clamp terminals



Input terminals 2× 16 mm²Output terminals per output 2× 1.5 mm²Alarm terminals 2.5 mm²

Bridging concept two sides, with spring clamp terminals or bridge set (max. 40 A)

Mounting method	DIN-rail mountable TH35 (EN 60715)
Dimensions H×W×D	90×70×80 mm
Temperature range	0...+55 °C (storage temperature -40...+80 °C)

Commercial data

country of origin	CZ
customs tariff number	85363010
EAN	4048879328920
eClass	27141901
Packaging unit	1

Sketch

Product may differ from Image