
3' x 60', Red-Black, Brush Step® Entrance Mat, 109

Product Images



Short Description

- **PROTECTS YOUR FLOOR** - If you're tired of having a wet/soggy entrance rug or worried about slips, trips, and falls, this all weather mat is right for you. The NoTrax floor mat is the best defense to keep water, snow, salt and debris from being tracked inside. The poly fibers absorb moisture, while the impermeable vinyl backing prevents moisture from reaching the floor.
- **EASY TO USE** - The Brush Step design has a unique double rib high/low design which helps get in between the sole tread of shoes for simple cleaning and drying. The vinyl back helps keep the rug in place to prevent slips, trips and falls. The minimalist low design makes it easy to vacuum. When used as a door mat, it gives way for doors to easily open, and as a chairmat, allows chairs to roll freely.
- **DURABLE/LONG LASTING** -No need to worry about replacing this indoor entrance mat frequently. Its sleek design makes it suitable for areas with medium traffic. This rug has the strength of a commercial mat with a sleek design that can hold up to everyday use.

Description

The low profile entry rug Brush Step® features a lighter-weight double rib high/low design that performs the scraping function of the mat. The ribbed surface brushes, channels, and conceals dirt and debris and is the perfect choice for light to medium traffic areas.

Specifications

Model No	109R0036RB
Color	Red/Black
Dimensions	3ft x 60ft
Thickness	5/16in
UPC	662641864092
Brand	NoTrax
Available Colors	Brown; Charcoal
Roll Sizes	3'x60', 4'x60', 6'x60'
Custom Lengths	3', 4' and 6' widths (up to 60' long)
Standard sizes	2'x3', 3'x4', 3'x5', 3'x6', 3'x10', 4'x6', 4'x8'
Group	Entrance Matting
Environment	Indoor
Recommended Use	For placement inside entrances of schools, offices, shops
Special Remarks	Brush Step® is comparable to most competitors' "best" rib mat
Edges	Vinyl borders
Usage Intensity	Light traffic
Surface Detail	Ribbed
Backing	Black vinyl (DOP free)
Process	Needle punched
Pallet Quantity	4
Pile Weight Oz	16
Weight Lbs/sqft	0.5
Thickness Inch	5/16in
Fire Rating US	Pass

REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Dust Control Rating	Good
Water Retention Rating	Good
Crush Resistance Rating	Good
Function Appearance Rating	Better