

# 3' x 6', Brown, Heritage Rib™ Scraper Entrance Mat, 117

## Product Images



## Short Description

- A heavier-weight double rib high/low design that performs the scraping function of the mat (Note: ribs run length of mat)
- 22 ounces of needle-punched yarn per square yard
- Low profile to perform in narrow clearance doorways
- Vinyl backing ensures minimal buckling and mat movement

## Description

---

Heritage Rib™ offers a heavier-weight double rib high/low design that performs the scraping function of the mat. This medium to heavy traffic entrance mat is intended for areas that need extra moisture retention and scraping action. Heritage Rib™ has 33% more carpet than many competitors' "best" rib mats. Heavy-weight vinyl non-slip backing ensures minimum movement.

## Specifications

---

|                  |   |
|------------------|---|
| Model No         | 117S0036BR  |
| Color            | Brown   |
| Dimensions       | 3ft x 6ft   |
| Thickness        | 3/8in   |
| UPC              | 662641608078  |
| Available Colors | Brown; Charcoal; Green; Red/Black   |
| Roll Sizes       | 3'x60', 4'x60', 6'x60'  |
| Custom Lengths   | 3', 4' and 6' widths (up to 60' long)   |
| Standard sizes   | 2'x3', 3'x4', 3'x5', 3'x6', 3'x10', 4'x6', 4'x8'  |
| Group            | Entrance Matting  |
| Environment      | Indoor  |
| Recommended Use  | For placement inside entrances of schools, offices, shops                               |
| Special Remarks  | Heritage Rib™ has 33% more carpet than many competitors' "best" Rib mats                |
| Surface          | Ribbed  |
| Edges            | Vinyl borders   |
| Usage Intensity  | Medium traffic  |
| Backing          | Black vinyl (DOP free)  |
| Process          | Needle punched  |
| Pallet Quantity  | 36  |
| Pile Weight Oz   | 22  |
| Weight Lbs/sqft  | 0.7   |
| Thickness Inch   | 3/8in   |
| Fire Rating US   | Pass  |
| REACH Compliant  | Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals). |

|                            |        |
|----------------------------|--------|
| Dust Control Rating        | Better |
| Water Retention Rating     | Better |
| Crush Resistance Rating    | Best   |
| Function Appearance Rating | Best   |