

## 3' x 10', Brown, Arrow Trax® Low Profile Scraper Entrance Mat, 118

### Product Images



### Short Description

- The high/low herringbone carpet design is attractive and functional as it scrapes debris and channels it away from shoes regardless of traffic flow
- A full 40 ounces of needle-punched yarn per square yard
- Low profile to perform in narrow clearance doorways
- Vinyl backing ensures minimal buckling and mat movement

## Description

---

Arrow Trax® mats provide exceptional performance in highly visible areas that require a subtly attractive yet functional matting product. The durable herringbone pattern offers non-directional scraping action and moisture retention, and a full 40 ounces of needle-punched yarn per square yard provides the highest degree of crush resistance in heavy traffic areas. Heavy-weight vinyl non-slip backing ensures minimum movement.

## Specifications

|                  |                                                                                                              |
|------------------|--------------------------------------------------------------------------------------------------------------|
| Model No         | 118S0310BR                                                                                                   |
| Color            | Brown                                                                                                        |
| Dimensions       | 3ft x 10ft                                                                                                   |
| Thickness        | 3/8in                                                                                                        |
| UPC              | 662641609396                                                                                                 |
| Brand            | NoTrax                                                                                                       |
| Available Colors | Autumn Black; Brown; Charcoal; Gray                                                                          |
| Roll Sizes       | 3'x60', 4'x60', 6'x60'                                                                                       |
| Custom Lengths   | 3', 4' and 6' widths (up to 60' long)                                                                        |
| Standard sizes   | 2'x3', 3'x4', 3'x5', 3'x6', 3'x10', 4'x6', 4'x8'                                                             |
| Group            | Entrance Matting                                                                                             |
| Environment      | Indoor                                                                                                       |
| Recommended Use  | For placement inside entrances in schools, universities, public buildings, sports facilities, shopping malls |
| Special Remarks  | A combination of 4 deniers of yarn make this an extremely long-lasting mat                                   |
| Edges            | Vinyl borders                                                                                                |
| Usage Intensity  | Heavy traffic                                                                                                |
| Surface Detail   | Chevron Pattern                                                                                              |
| Backing          | Black vinyl (DOP free)                                                                                       |
| Process          | Needle punched                                                                                               |
| Pallet Quantity  | 20                                                                                                           |
| Pile Weight Oz   | 40                                                                                                           |
| Weight Lbs/sqft  | 0.7                                                                                                          |
| Thickness Inch   | 3/8in                                                                                                        |
| Fire Rating US   | Pass                                                                                                         |

|                            |                                                                                         |
|----------------------------|-----------------------------------------------------------------------------------------|
| REACH Compliant            | Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals). |
| Dust Control Rating        | Best                                                                                    |
| Water Retention Rating     | Best                                                                                    |
| Crush Resistance Rating    | Best                                                                                    |
| Function Appearance Rating | Superior                                                                                |