

Entrance Moisture Mat, Dante™, 131

Product Images



Short Description

- Densely tufted cut-pile Decalon® provides moisture retention
- 25 ounces of tufted cut-pile yarn per square yard
- Low profile to perform in narrow clearance doorways
- Vinyl backing ensures minimal buckling and mat movement

Description

Dante™ moisture mat is made with a densely tufted cut-pile Decalon® construction that is a step above the look-alikes and provides much greater moisture retention. 25 ounces of tufted yarn per square yard make it the perfect product for all medium traffic areas including entrances and lobbies. A vinyl non-slip backing helps to minimize mat movement. Dante™ has 33% more carpet than the competitors "best" Olefin mats.

Specifications

Model No	131
Available Colors	Brown; Charcoal
Overall Thickness	3/8; 5/16
Roll Sizes	3'x 60'; 4'x 60'; 6'x 60'
Custom Lengths	3', 4' and 6' widths (up to 60' long)
Standard sizes	2'x 3'; 3'x 4'; 3'x 5'; 3'x 6'; 3'x 10'; 4'x 6'; 4'x 8'
Group	Entrance Matting
Environment	Indoor
Recommended Use	For placement inside entrances of schools, offices, shops
Special Remarks	Dante™ has 33% more carpet than many competitors' "best" Olefin mats
Surface	Rich Monochrome Colors
Edges	Vinyl borders
Usage Intensity	Medium duty
Material Specifications	Decalon® yarns
Backing	Black vinyl (DOP free)
Process	Tufting
Pile Weight Oz	25
Weight Lbs/sqft	0.65
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Dust Control Rating	Better
Water Retention Rating	Best
Crush Resistance Rating	Better
Function Appearance Rating	Better

Product Options

Color:	Brown
	Charcoal
Dimensions:	2ft x 3ft
	3ft x 10ft
	3ft x 4ft
	3ft x 5ft
	3ft x 60ft
	3ft x 6ft
	3ft x Specify Length
	4ft x 60ft
	4ft x 6ft
	4ft x 8ft
	4ft x Specify Length
	6ft x 60ft
	6ft x Specify Length
thickness_filter:	3/8in
	5/16in