


3/8" x 6' x Custom Length, Charcoal, Dante™ Moisture Entrance Mat, 131

Product Images



Short Description

- Densely tufted cut-pile Decalon® provides moisture retention
- 25 ounces of tufted cut-pile yarn per square yard
- Low profile to perform in narrow clearance doorways
- Vinyl backing ensures minimal buckling and mat movement

Description

Dante™ moisture mat is made with a densely tufted cut-pile Decalon® construction that is a step above the look-alikes and provides much greater moisture retention. 25 ounces of tufted yarn per square yard make it the perfect product for all medium traffic areas including entrances and lobbies. A vinyl non-slip backing helps to minimize mat movement. Dante™ has 33% more carpet than the competitors "best" Olefin mats.

Specifications

Model No	131C0072CH
Color	Charcoal
Dimensions	6ft x Specify Length
Thickness	3/8in
UPC	662641683532
Brand	NoTrax
Available Colors	Brown; Burgundy; Charcoal; Gray; Green; Navy; Red/Black
Roll Sizes	3'x60', 4'x60', 6'x60'
Custom Lengths	3', 4' and 6' widths (up to 60' long)
Standard sizes	2'x3', 3'x4', 3'x5', 3'x6', 3'x10', 4'x6', 4'x8'
Group	Entrance Matting
Environment	Indoor
Recommended Use	For placement inside entrances of schools, offices, shops
Special Remarks	Dante™ has 33% more carpet than many competitors' "best" Olefin mats
Edges	Vinyl borders
Usage Intensity	Medium duty
Material Specifications	Decalon® yarns
Surface Detail	Rich Monochrome Colors
Backing	Black vinyl (DOP free)
Process	Tufting
Pile Weight Oz	25
Weight Lbs/sqft	0.65
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).

Dust Control Rating	Better
Water Retention Rating	Best
Crush Resistance Rating	Better
Function Appearance Rating	Better