



3' x 5', Slate Blue, Aqua-Trap® Moisture and Scrape Entrance Mat, 150

Product Images



Short Description

- Molded dome pattern facilitates scraping and drying, retaining moisture and debris within its patented Aqua-Dam™ border
- Raised rubber border retains moisture and debris
- Carpet-to-edge (CTE™) construction to blend with its surroundings
- Anti-Microbial carpet treatment stops odor causing bacteria and germs
- 20 ounces of tufted yarn per square yard

Description

Aqua-Trap® is a unique yet highly functional indoor/outdoor entrance mat with a molded dome pattern that facilitates the scraping and drying process while a patented raised “Aqua Dam™” border forms a perimeter on all four sides of the mat retains moisture and debris. Aqua-Trap® features an antimicrobial carpet treatment that stops odor causing bacteria and germs at the entrance. An extremely durable rubber backed mat, Aqua-Trap® has a highly fashionable look that features carpet-to-the-edge (CTE™) to blend with its surroundings and contemporary color choices to match any décor.

Specifications

Model No	150S0035BU
Color	Slate Blue
Dimensions	3ft x 5ft
Thickness	3/8in
UPC	662641011649
Brand	NoTrax
Special Price Type	Sale
Available Colors	Blue; Brown; Charcoal; Gray; Red/Black
Custom Lengths	3' and 4' widths (5'3" up to 60' long)
Standard sizes	2'x3', 3'x4', 3'x5', 3'x10', 4'x6', 4'x10'
Group	Entrance Matting
Environment	Indoor
Recommended Use	For placement inside entrances of hotels, shops, department stores, schools, universities, restaurants, supermarkets.
Special Remarks	Extremely durable, yet highly fashionable look featuring carpet to-the-edge to blend with its surroundings
Edges	Fabric covered borders
Usage Intensity	Heavy traffic
Custom Description	Available in stock sizes and in custom lengths. Available colors in charcoal, brown, gray, burgundy, red/black, hunter green, slate blue
Surface Detail	Raised Dome Design
Backing	Natural rubber
Process	Tufting
Pallet Quantity	36
Pile Weight Oz	20
Weight Lbs/sqft	1.17

Thickness Inch	3/8in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Dust Control Rating	Superior
Water Retention Rating	Superior
Crush Resistance Rating	Best
Function Appearance Rating	Superior

Prop 65

⚠️WARNING:This product can expose you to 2-mercaptobenzothiazole which is known to the State of California to cause cancer. For more information, visit www.P65Warnings.ca.gov.