


# 4' x 6', Blue, Diamond CTE™ Moisture and Debris Entrance Mat, 151

## Product Images





## Short Description

---

- High/low diamond pattern facilitates scraping and keeps moisture and debris away from foot traffic
- Raised rubber carpet-to-edge (CTE™), bordered on all 4 sides to trap moisture and debris
- Crumb rubber backing
- 26 ounces of tufted yarn per square yard for increased moisture retention, and easier cleaning
- Low profile to perform in narrow clearance doorways

## Description

---

Diamond CTE™ is a crumb rubber-backed entrance mat intended for use in light to medium traffic areas. The non-directional raised, crushproof diamond pattern of Diamond CTE™ scrapes and cleans, while the carpet-to-edge (CTE™) perimeter entraps dirt and moisture for water and soil control. Crumb rubber underside of the mat grips the underlying surface minimizing mat movement.

## Specifications

---

Model No	151S0046BU
Color	Blue
Dimensions	4ft x 6ft
Thickness	3/8in
UPC	662641887794
Available Colors	Brown; Charcoal; Gray
Standard sizes	2'x3', 3'x5', 4'x6'
Group	Entrance Matting
Environment	Indoor/Outdoor
Recommended Use	For placement inside entrances in schools, universities, public buildings, sports facilities, shopping malls
Special Remarks	Entranceways and lobbies, all light to medium traffic areas
Surface	Raised Diamond Pattern
Edges	Fabric covered borders
Usage Intensity	Light traffic
Custom Description	Available in stock sizes. Available colors in charcoal, blue, brown.
Backing	Crumb rubber
Process	Tufting
Pile Weight Oz	26
Weight Lbs/sqft	0.9
Thickness Inch	3/8in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Dust Control Rating	Good
Water Retention Rating	Good

Crush Resistance Rating	Good
Function Appearance Rating	Better

## Prop 65

---

**⚠️WARNING:** This product can expose you to di-2-ethylhexyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).