


3' x 5', Charcoal, Waffle CTE™ Moisture and Scraper Entrance Mat, 152

Product Images





Short Description

- High/low waffle pattern facilitates scraping and keeps moisture and debris away from foot traffic
- Raised rubber carpet-to-edge (CTE™), bordered on all 4 sides to trap moisture and debris
- Crumb rubber backing
- 26 ounces of tufted yarn per square yard for increased moisture retention, and easier cleaning
- Low profile to perform in narrow clearance doorways

Description

Waffle CTE™ is a crumb rubber-backed entrance waffle mat intended for use in light to medium traffic areas. The classic raised, crushproof waffle pattern of Waffle CTE™ scrapes and cleans, while the carpet-to-edge (CTE™) perimeter entraps dirt and moisture for water and soil control. Crumb rubber underside of the mat grips the underlying surface minimizing mat movement.

Specifications

Model No	152S0035CH
Color	Charcoal
Dimensions	3ft x 5ft
Thickness	1/2in
UPC	662641891982
Standard sizes	2'x3', 3'x5', 4'x6'
Group	Entrance Matting
Environment	Indoor/Outdoor
Recommended Use	For placement inside entrances in schools, universities, public buildings, sports facilities, shopping malls
Special Remarks	Entranceways and lobbies, all light to medium traffic areas
Surface	Raised Waffle Patten
Edges	Fabric covered borders
Usage Intensity	Light traffic
Custom Description	Available in stock sizes. Available colors in charcoal, blue, brown.
Material Specifications	Polypropylene
Backing	Crumb rubber
Process	Tufting
Pallet Quantity	36
Pile Weight Oz	26
Weight Lbs/sqft	0.9
Thickness Inch	1/2in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Dust Control Rating	Good

Water Retention Rating	Good
Crush Resistance Rating	Good
Function Appearance Rating	Better

Prop 65

⚠️WARNING: This product can expose you to di-2-ethylhexyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.