


---

# 32" x 39", Black-Yellow, Sani-Trax<sup>®</sup> Plus Shoe Sanitizer Mat, 351

## Product Images

---





## Short Description

---

- Tough rubber compound resists most chemicals and variations in temperature
- Overall mat thickness is 2.5" and holds up to 5 gallons of sanitizing solution
- Thick containment border stands 1 7/8" higher than finger scrapers to contain disinfectant and contaminants
- Thousands of flexible rubber fingers provide scrubbing action
- Suction cups on underside help to minimize mat movement

## Description

---

Sani-Trax® Plus is an entrance disinfectant foot mat that cleans and sanitizes shoes at entrances to sensitive areas such as food processing plants or laboratories. Thousands of flexible fingers provide an automatic scrubbing action that dislodges contaminants from footwear. A thick rubber border allows the mat to hold up to 5 gallons of disinfectant solution and as traffic passes, the rubber tips bend to immerse the soles of shoes in the disinfectant solution. A tough rubber compound is designed to resist most chemicals and variations in temperature, while suction cups on the underside of the mat keep it in place.

## Specifications

Model No	351S3239YB
Color	Black/Yellow
Dimensions	32in x 39in
Thickness	2 1/2in
UPC	662641888012
Standard sizes	32"x39"
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry Areas
Recommended Use	At doorways, starter rooms, packaging areas, laboratories, employee locker rooms, break rooms, refuse areas and receiving areas. Any place where spread of contamination needs to be limited.
Special Remarks	Use quaternary ammonium, iodine, chlorine, or any other sanitizer but always test it's concentration. Most sanitizers are concentrated and must be diluted before use in a footbath. Follow label directions for appropriate dilutions.
Surface	Flexible Rubber Bristles
Edges	Rubber borders
Usage Intensity	Heavy traffic
Material Specifications	Tough rubber compound
Process	Compression Molding
Pallet Quantity	36
Weight Lbs/sqft	3.8
Thickness Inch	2 1/2in
Fire Rating US	Pass