


# Anti-Fatigue Mat Sof-Tred™ 411

## Product Images







## Short Description

---

- Non-directional pebble-texture embossed mat
- Basic anti-fatigue protection provided
- Closed cell PVC foam relieves leg and back discomfort
- Provides an insulated barrier to cold floors
- Perfect anti-fatigue mat for dry applications
- Beveled edges on all 4 sides

## Description

---

Sof-Tred™ anti fatigue foam mat has an embossed pebble-texture top surface that enhances the mat's slip resistance while providing increased basic worker fatigue relief. The PVC closed cell foam construction relieves leg and back discomfort while providing a barrier to cold floors. Sof-Tred™ is intended for applications where basic anti-fatigue relief is required at a low cost.

## Specifications

Model No	411
Available Colors	Black; Black/Yellow
Overall Thickness	3/8; 9/16
Roll Sizes	3/8" x 2'x 60'; 3/8" x 3'x 60'; 3/8" x 4'x 60'; 3/8" x 6'x 60'; 9/16" x 2'x 60'; 9/16" x 3'x 60'; 9/16" x 4'x 60'; 9/16" x 6'x 60'
Custom Lengths	2', 3' and 4' widths (up to 60' long)
Standard sizes	3/8" x 2'x 3'; 3/8" x 3'x 5'; 3/8" x 3'x 12'; 9/16" x 2'x 3'; 9/16" x 3'x 5'; 9/16" x 3'x 12'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Where basic anti-fatigue and anti-slip properties are needed at a low cost
Surface	Structured Pebble Pattern
Edges	Beveled edges on all sides
Usage Intensity	Light duty
Custom Description	Available in stock and rolls sizes and in custom lengths. Available colors in black/yellow and black.
Material Specifications	Closed Cell Polyvinylchloride
Backing	Closed Cell Polyvinylchloride
Process	Foaming
Weight Lbs/sqft	0.53
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Good

Slip Resistance Rating	Good
Wear Resistance Rating	Good

## Product Options

---

Color:	Black
	Black/Yellow
Dimensions:	2ft x 3ft
	2ft x 60ft
	2ft x Specify Length
	3ft x 12ft
	3ft x 5ft
	3ft x 60ft
	3ft x Specify Length
	4ft x 60ft
	4ft x Specify Length
	6ft x 60ft
	thickness_filter:
9/16in	