
2' x 3', Blue, Marble Sof-Tyle™ Anti Fatigue Mat, 470

Product Images





Short Description

- Heavy-duty vinyl marble-pattern top surface combined with a dense closed cell PVC foam base provides added cushioning comfort
- Smooth attractive surface easy to sweep clean
- UniFusion™ bond guaranteed for the life of the mat
- Redstop™ non-slip backing to reduce mat slippage
- Beveled edges on all 4 sides

Description

Marble Sof-Tyle™ is an anti-fatigue floor mat provides comfort and ergonomic support and complements any décor with a stylish smooth marble-pattern design. The durable vinyl top surface is easy to sweep clean or damp mop and is combined with a dense closed cell foam base utilizing NoTrax® exclusive UniFusion™ technology. This virtually eliminates the possibility of de-lamination. NoTrax® laminate floor mats that come with RedStop™, a uniquely engineered non-slip backing technology, eliminates the slipping and sliding of floor mats on smooth surface flooring such as tile, wood, marble, and treated concrete For dry applications such as lab testing area, check-out counters, order fulfillment lines and pharmacies. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat.

Specifications

| | |
|-------------------------|---|
| Model No | 470S2436BU |
| Color | Blue |
| Dimensions | 2ft x 3ft |
| Thickness | 1/2in |
| UPC | 662641641983 |
| Available Colors | Gray |
| Custom Lengths | 2', 3' and 4' widths (up to 75' long) |
| Group | Ergonomic, Anti-fatigue & Safety Matting |
| Environment | Dry Areas |
| Special Characteristics | Coefficient of friction NSF certified Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals |
| Recommended Use | For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations. |
| Special Remarks | Recommended where there is a minimal amount of debris in the environment and a concern for the mat to match a décor. |
| Surface | Marble Pattern |
| Edges | Beveled edges on all sides |
| Usage Intensity | Heavy duty |
| Material Specifications | PVC on microcellular vinyl base |
| Backing | Closed Cell Polyvinylchloride with RedStop™ slip-resistant backing |
| Process | Lamination |
| Weight Lbs/sqft | 1.2 |
| Thickness Inch | 1/2in |
| Fire Rating US | Pass |
| REACH Compliant | Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals). |

| | |
|------------------------|------|
| Anti-Fatigue Rating | Best |
| Slip Resistance Rating | Best |
| Wear Resistance Rating | Best |

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.