
4' x Custom Length, Black, Pebble Trax® Anti Fatigue Mat, 480

Product Images



Short Description

- The pebble embossed rubber top surface is combined with a dense closed cell PVC foam base
- Spark resistant
- UniFusion™ bond guaranteed for the life of the mat
- Redstop™ non-slip backing to reduce mat slippage
- Beveled edges on all 4 sides

Description

Pebble Trax® is an anti-fatigue floor mat that offers comfort and ergonomic support in dry environments such as assembly lines, lab areas, machine workstations and packing areas. The pebble-embossed rubber top provides non-directional traction and is easy to clean and resists exposure to sparks from welding. Made with a resilient SBR rubber compound, the top surface is combined with a dense closed cell foam base utilizing Notrax® exclusive UniFusion™ technology. This virtually eliminates the possibility of de-lamination. All Notrax® laminate floor mats come standard with RedStop™, a uniquely engineered non-slip backing technology that eliminates the slipping and sliding of floor mats on smooth surface flooring such as tile, wood, marble, and treated concrete. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat.

Specifications

Model No	480C0048BL
Color	Black
Dimensions	4ft x Specify Length
Thickness	1/2in
UPC	662641673557
Brand	NoTrax
Available Colors	Black
Custom Lengths	2', 3' and 4' widths (up to 75' long)
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Coefficient of friction NSF1 certified
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Easy to clean non-directional top surface
Edges	Beveled edges on all sides
Usage Intensity	Heavy duty
Material Specifications	Rubber on microcellular vinyl base
Surface Detail	Structured Pebble Pattern
Backing	Closed Cell Polyvinylchloride with RedStop™ slip-resistant backing
Process	Lamination
Weight Lbs/sqft	1.6
Thickness Inch	1/2in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Best

Slip Resistance Rating	Best
Wear Resistance Rating	Best