



4' x Custom Length, Black, Bubble Trax® Anti Fatigue Mat, 482

Product Images



Short Description

- Heavy-duty vinyl bubble mat top surface combined with a dense closed cell PVC foam base provides added cushioning comfort
- UniFusion™ bond guaranteed for the life of the mat
- Redstop™ non-slip backing to reduce mat slippage
- Beveled edges on all 4 sides
- Certified by the NFSI (National Floor Safety Institute)

Description

Bubble Trax® is an unique high performance anti-fatigue floor mat with a bubble top surface design providing extreme ergonomic comfort and durability. Bubble Trax® combines a heavy-duty vinyl top surface with a dense sponge backing utilizing NoTrax® exclusive UniFusion™ technology. This virtually eliminates the possibility of de-lamination. NoTrax® laminate floor mats that come with RedStop™, a uniquely engineered non-slip backing technology, eliminates the slipping and sliding of floor mats on smooth surface flooring such as tile, wood, marble, and treated concrete. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat. Extremely well suited for multi-shift operations in dry work area where the worker is standing for prolonged periods of time; workstations, assembly lines.

Specifications

Model No	482C0048BL
Color	Black
Dimensions	4ft x Specify Length
Thickness	1/2in
UPC	662641843387
Brand	NoTrax
Roll Sizes	2'x72', 3'x72', 4'x72', 5'x72' * Gray not available in 4'x72' and 5'x72' widths
Custom Lengths	2', 3', 4' and 5' widths (up to 72' long) * Gray not available in 4' and 5' widths
Standard sizes	2'x3', 3'x5'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Coefficient of friction NSF1 certified Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, production lines, assembly lines, CNC machines, metal working for individual workstations and custom work platforms
Special Remarks	Bubble-top design for additional comfort and ergonomic support. Ideal for multi-shift environments.
Edges	Beveled edges on all sides
Usage Intensity	Heavy duty
Material Specifications	PVC on microcellular vinyl base
Surface Detail	Industrial Bubble Pattern
Backing	Closed Cell Polyvinylchloride with RedStop™ slip-resistant backing
Process	Lamination
Weight Lbs/sqft	1.3
Thickness Inch	1/2in

Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Best
Slip Resistance Rating	Best
Wear Resistance Rating	Best

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.