





Anti-Fatigue Mat Rolls Diamond Cushion™ 508

Product Images





Short Description

- Non-directional diamond plate textured embossed pattern
- Basic anti-fatigue protection provided
- Closed cell PVC foam relieves leg and back discomfort
- Provides an insulated barrier to cold floors
- Perfect anti-fatigue mat for dry applications
- Beveled edges on all 4 sides

Description

Diamond-Cushion™ anti fatigue mat is an embossed diamond plate texture top surface that enhances the mats slip resistance while providing increased worker fatigue relief. The PVC closed cell foam construction relieves leg and back discomfort while providing a barrier to cold floors. Diamond-Cushion™ is intended for applications where basic anti-fatigue relief is required at a low cost.

Specifications

Model No	508
Available Colors	Black; Black/Yellow
Overall Thickness	1/2
Roll Sizes	2'x 60'; 3'x 60'; 4'x 60'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Rolls sizes make it the perfect low cost solution for applications requiring longer mats
Surface	Industrial Diamond Plate
Edges	Beveled edges on all sides
Usage Intensity	Light duty
Custom Description	Available in rolls sizes and in custom lengths. Available colors in black/yellow and black
Cleaning Remark	Sweep regularly or dry mop the surface and the back of the mat. The surface can be damp-mopped with a mild soap/detergent.
Material Specifications	Closed Cell Polyvinylchloride
Backing	Closed Cell Polyvinylchloride
Process	Foaming
Weight Lbs/sqft	0.53
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Good
Slip Resistance Rating	Better

Wear Resistance Rating

Good

Product Options

Color:

Black

Black/Yellow

Dimensions:

2ft x 60ft

3ft x 60ft

4ft x 60ft