

6" x 12", Male, Yellow, Cushion-Lok™ Ramp, 520

Product Images



Short Description

- A tough PVC based workstation mat made from 100% recycled materials (black only)
- Porthole drainage system removes liquids and debris from worker platform
- Raised footing design elevates the worker out of the spillage
- Stock size mats have beveled edges permanently affixed on 3 sides for a true workstation mat
- Accessories:
 - 12x12" Tile (black only)
 - 6x12" Ramps (yellow only)
 - 6x6" Corners (yellow only)

Description

Cushion-Lok™ is a tough PVC based workstation mat intended for wet environments where resistance to harsh industrial chemicals is a necessity. Cushion-Lok™ has hundreds of portholes to facilitate drainage while the worker is elevated on a series of blades to increase traction and keep the worker out of the spillage. Cushion-Lok™ is manufactured from 100% recycled PVC for greater resistance to industrial chemicals, cutting fluids, oils and greases. Create your own workstation configuration or select an assembled stock size.

Specifications

Model No	520M0612YL
Color	Yellow
Dimensions	0.5ft x 1ft
Thickness	7/8in
UPC	662641643475
Brand	NoTrax
Available Colors	Black; Black/Yellow
Standard sizes	6"x12"
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Oily Areas
Special Characteristics	Available yellow borders along sides comply with OSHA code 1910-144 Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals Resistant to most chemicals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Factory-assembled custom configurations available - Call Customer Service for more information (800) 621-2802
Usage Intensity	Heavy duty
Installation	The modular matting system consists of 12in x 12in modular tiles that interlock for on site installation with a rubber hammer.
Material Specifications	PVC
Surface Detail	Perforated Drainage Pattern
Process	Injection Molding
Weight Lbs/sqft	1
Thickness Inch	7/8in
Fire Rating US	Pass

REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Best
Slip Resistance Rating	Best
Wear Resistance Rating	Best

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.