

3' x 3', Red, Sanitop® Anti Fatigue Mat, 562RD

Product Images



Short Description

- Durable rubber compound
- Molded alternating large/small hole drainage system keeps moisture and debris free from work area
- Raised pattern surround large holes to channel drainage and provide worker traction
- 100% Nitrile Grease Resistant
- Molded in beveled edges on all 4 sides

Description

Sanitop® is made from a durable rubber compound designed to withstand harsh chemicals while creating a slip resistant surface. Available in general purpose (black) and heavy-duty Nitrile (red) rubber compounds for varying degrees of grease and oil protection. A large and small hole drainage system channels liquid and debris away from the work area. Molded in beveled edges on all four sides eliminates trip hazards. Sanitop® offers a simple, economical solution for wet environments in many industrial or food service application.

Specifications

Model No	562S0033RD
Color	Red
Dimensions	3ft x 3ft
Thickness	1/2in
UPC	662641768697
Brand	NoTrax
Available Colors	Red
Standard sizes	3'x5', 3'x10', 3'x20'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Wet/Dry and Greasy Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	Food processing, professional kitchens, cooking lines, food preparation areas, bars and cleaning areas
Special Remarks	It's lightweight workstation design with molded beveled edges make it easier to pickup or move for cleaning
Edges	Molded beveled edges on all sides
Usage Intensity	Medium duty
Material Specifications	75% Nitrile rubber
Surface Detail	Large Drainage Holes
Process	Compression Molding
Pallet Quantity	42
Weight Lbs/sqft	1.4
Thickness Inch	1/2in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Best

Slip Resistance Rating	Best
Wear Resistance Rating	Best
Grease Resistance Rating	Best