

3' x Custom Length, Black, Diamond Plate Runner™ Anti-Slip Message Mats, 738

Product Images



Short Description

- Heavy-duty rubber diamond design improves traction and comfort
- Insulates floor and creates a silencing effect
- Oil, grease, and chemical resistant
- Provides barrier to cold floors and floor protection
- Low profile to eliminate trip hazards and allow for cart traffic

Description

The high profile diamond-embossed top surface yields exceptional traction from any direction. Made of durable rubber, this runner is easy to sweep clean and has a low profile allowing for easy on/off cart traffic. Diamond Plate Runner™ is recommended for applications where safety and slip protection is needed with minimal anti-fatigue value such as aisles, warehouses, vending areas, and industrial passageways.

Specifications

Model No	738C0036BL
Color	Black
Dimensions	3ft x Specify Length
Thickness	5/32in
UPC	662641827066
Brand	NoTrax
Roll Sizes	2'x75', 3'x75', 4'x75'
Custom Lengths	2', 3', 4' and 5' widths (up to 150' long)
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	The diamond plate top surface provides additional traction
Edges	No borders
Usage Intensity	Light duty
Material Specifications	SBR Rubber
Surface Detail	Industrial Diamond Plate
Process	Calendering
Weight Lbs/sqft	0.8
Thickness Inch	5/32in
Anti-Fatigue Rating	Good
Slip Resistance Rating	Better
Wear Resistance Rating	Better

Prop 65

 **WARNING:** This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.