
3' x Custom Length, Black, V-Groove Corrugated Runner[™] Floor Protector Rubber Mat, 750

Product Images



Short Description

- Heavy-duty rubber corrugated rib-tooth design improves traction and comfort
- Insulates floor and creates a silencing effect
- Performs at low temperatures and is suitable for indoor and outdoor use
- Motor Vehicle Safety Standard #302 (Flame Test) - Pass
- Low profile to eliminate trip hazards and allow for cart traffic

Description

V-Groove Corrugated Runner™ is made from a long-lasting rubber compound that features a rib-tooth design and provides sure footing and floor protection. This corrugated-rubber-mat also creates a barrier to cold flooring substrates, and has a silencing effect over noisy tile. The low profile corrugated rubber mat allows for easy on/off cart traffic and can also be used as a liner for maintenance and tool carts.

Specifications

Model No	750C0036BL
Color	Black
Dimensions	3ft x Specify Length
Thickness	1/8in
UPC	662641649552
Brand	NoTrax
Available Colors	Black; Gray
Roll Sizes	2'x75', 3'x75', 4'x75', 6'x75', 2'x150', 3'x150', 4'x150'
Custom Lengths	2', 3', 4' and 6' widths (up to 150' long)
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals
Recommended Use	For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	Recommend for applications that require a little more traction. Can be used as a liner for maintenance and tool carts
Edges	No borders
Usage Intensity	Light duty
Material Specifications	SBR Rubber
Surface Detail	Lengthwise Corrugated Rib Pattern
Process	Calendering
Weight Lbs/sqft	0.8
Thickness Inch	1/8in
Temperature Range	- 40 ° C up to + 120 ° C
Fire Rating US	Pass

REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Good
Slip Resistance Rating	Better
Wear Resistance Rating	Best

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.