

---

## 4' x 75', Black, V-Groove Corrugated Runner<sup>™</sup> Floor Protector Rubber Mat, 750

### Product Images

---



## Short Description

---

- Heavy-duty rubber corrugated rib-tooth design improves traction and comfort
- Insulates floor and creates a silencing effect
- Performs at low temperatures and is suitable for indoor and outdoor use
- Motor Vehicle Safety Standard #302 (Flame Test) - Pass
- Low profile to eliminate trip hazards and allow for cart traffic

## Description

---

V-Groove Corrugated Runner™ is made from a long-lasting rubber compound that features a rib-tooth design and provides sure footing and floor protection. This corrugated-rubber-mat also creates a barrier to cold flooring substrates, and has a silencing effect over noisy tile. The low profile corrugated rubber mat allows for easy on/off cart traffic and can also be used as a liner for maintenance and tool carts.

## Specifications

|                         |                                                                                                                             |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Model No                | 750R0048BL                                                                                                                  |
| Color                   | Black                                                                                                                       |
| Dimensions              | 4ft x 75ft                                                                                                                  |
| Thickness               | 1/8in                                                                                                                       |
| UPC                     | 662641731011                                                                                                                |
| Brand                   | NoTrax                                                                                                                      |
| Available Colors        | Black; Gray                                                                                                                 |
| Roll Sizes              | 2'x75', 3'x75', 4'x75', 6'x75', 2'x150', 3'x150', 4'x150'                                                                   |
| Custom Lengths          | 2', 3', 4' and 6' widths (up to 150' long)                                                                                  |
| Group                   | Ergonomic, Anti-fatigue & Safety Matting                                                                                    |
| Environment             | Dry Areas                                                                                                                   |
| Special Characteristics | Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals                     |
| Recommended Use         | For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations. |
| Special Remarks         | Recommend for applications that require a little more traction. Can be used as a liner for maintenance and tool carts       |
| Edges                   | No borders                                                                                                                  |
| Usage Intensity         | Light duty                                                                                                                  |
| Material Specifications | SBR Rubber                                                                                                                  |
| Surface Detail          | Lengthwise Corrugated Rib Pattern                                                                                           |
| Process                 | Calendering                                                                                                                 |
| Weight Lbs/sqft         | 0.8                                                                                                                         |
| Thickness Inch          | 1/8in                                                                                                                       |
| Temperature Range       | - 40 ° C up to + 120 ° C                                                                                                    |
| Fire Rating US          | Pass                                                                                                                        |

|                        |                                                                                         |
|------------------------|-----------------------------------------------------------------------------------------|
| REACH Compliant        | Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals). |
| Anti-Fatigue Rating    | Good                                                                                    |
| Slip Resistance Rating | Better                                                                                  |
| Wear Resistance Rating | Best                                                                                    |

## Prop 65

---

**⚠️WARNING:** This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).