




---

# 3' x Custom Length, Black, Deep Freeze Mat™, 765

## Product Images

---



## Short Description

---

- Made from a tough rubber compound
- Raised knob solid top surface that enhances traction
- Tested to withstand temperatures to -40 Fahrenheit (approximately - 40° Celsius)
- Low profile allows for easy on/off cart traffic

## Description

---

The Deep Freeze Mat™ is the only rubber mat specifically formulated to perform in deep freeze environments. Tested to withstand temperatures to -40 degrees Fahrenheit, this anti-slip mat features a raised knob solid top surface to enhance traction, and is designed for use in meat lockers, walk-ins, and other specialty freezer applications.

## Specifications

|                        |                                                                                                                                                                  |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No               | 765C0036BL                                                                                                                                                       |
| Color                  | Black                                                                                                                                                            |
| Dimensions             | 3ft x Specify Length                                                                                                                                             |
| Thickness              | 3/8in                                                                                                                                                            |
| UPC                    | 662641753396                                                                                                                                                     |
| Brand                  | NoTrax                                                                                                                                                           |
| Available Colors       | Black                                                                                                                                                            |
| Custom Lengths         | 2', 3' and 4' widths (up to 60' long)                                                                                                                            |
| Standard sizes         | 2'x5', 2'x8', 3'x5', 3'x8', 4'x5', 4'x8'                                                                                                                         |
| Group                  | Ergonomic, Anti-fatigue & Safety Matting                                                                                                                         |
| Environment            | Wet/Dry and Oily Areas                                                                                                                                           |
| Recommended Use        | Restaurant kitchens, food prep, food processing environments                                                                                                     |
| Special Remarks        | The only rubber mat specifically formulated to perform in deep freeze environments. Withstand cold temperatures, anti-slip surface, low profile for cart traffic |
| Surface Detail         | Industrial Bubble Pattern                                                                                                                                        |
| Process                | Molding                                                                                                                                                          |
| Weight Lbs/sqft        | 1.6                                                                                                                                                              |
| Thickness Inch         | 3/8in                                                                                                                                                            |
| Fire Rating US         | Pass                                                                                                                                                             |
| REACH Compliant        | Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).                                                                          |
| Anti-Fatigue Rating    | Good                                                                                                                                                             |
| Slip Resistance Rating | Best                                                                                                                                                             |
| Wear Resistance Rating | Better                                                                                                                                                           |
| Comfort Rating         | Good                                                                                                                                                             |

Grease Resistance Rating

Good

## Prop 65

---

**⚠️WARNING:** This product can expose you to chemicals including diisodecyl phthalate which is known to the State of California to cause birth defects or reproductive harm, and 2-mercaptobenzothiazole which is known to the State of California to cause cancer. For more information, visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).