

---

## 2' x Custom Length, Black, Pebble Trax® Runner™ Floor Protector Mat, 780

### Product Images

---



## Short Description

---

- Heavy-duty rubber pebble-embossed design improves traction and comfort
- Insulates floor and creates a silencing effect
- Oil, grease, and chemical resistant
- Provides barrier to cold floors and floor protection
- Low profile to eliminate trip hazards and allow for cart traffic

## Description

---

The Pebble Trax® Runner™ is made with a resilient rubber compound and a pebble-embossed surface providing long-lasting traction and floor protection for a variety of industrial applications. This runner is the perfect product for long warehouse and store-room aiseways creating a barrier to cold floors. The low profile matting allows for easy on/off cart traffic.

## Specifications

|                         |                                                                                                                             |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Model No                | 780C0024BL                                                                                                                  |
| Color                   | Black                                                                                                                       |
| Dimensions              | 2ft x Specify Length                                                                                                        |
| Thickness               | 3/32in                                                                                                                      |
| UPC                     | 662641706064                                                                                                                |
| Brand                   | NoTrax                                                                                                                      |
| Custom Lengths          | 2', 3' and 4' widths (up to 156' long)                                                                                      |
| Group                   | Ergonomic, Anti-fatigue & Safety Matting                                                                                    |
| Environment             | Dry Areas                                                                                                                   |
| Recommended Use         | For placement in manufacturing plants, assembly lines, picking, packing and logistics warehouses, individual work stations. |
| Special Remarks         | Non-directional traction in longer runs                                                                                     |
| Edges                   | No borders                                                                                                                  |
| Usage Intensity         | Medium duty                                                                                                                 |
| Material Specifications | SBR Rubber                                                                                                                  |
| Surface Detail          | Structured Pebble Pattern                                                                                                   |
| Process                 | Calendering                                                                                                                 |
| Weight Lbs/sqft         | 0.8                                                                                                                         |
| Thickness Inch          | 3/32in                                                                                                                      |
| Fire Rating US          | Pass                                                                                                                        |
| Anti-Fatigue Rating     | Good                                                                                                                        |
| Slip Resistance Rating  | Better                                                                                                                      |
| Wear Resistance Rating  | Better                                                                                                                      |