




4' x Custom Length, Black-Yellow, Cushion-Stat[™] with Dyna-Shield[®] Anti Static Mat, 825

Product Images



Short Description

- Static dissipative PVC sponge. Absorbs static electricity keeping sensitive electronic circuitry safe
- PVC foam provides added cushioning comfort, relieves leg and back discomfort
- Non-directional pebble textured embossed mat maximizes worker comfort
- Exclusive Dyna-Shield® top surface manufactured directly into the mat for long lasting wear
- RG $10^6 - 10^9 \Omega$; RP $10^6 - 10^9 \Omega$

Description

Cushion Stat™ w/ Dyna-Shield® is a dissipative/anti-static mat that is specially formulated to absorb static electricity keeping sensitive electronic circuitry safe from damage. The anti-fatigue properties are designed to provide traction with its non-directional pebble embossed top surface that allows for sure footing and is easy to sweep clean. The Notrax® exclusive Dyna-Shield® PVC foam is manufactured with a tough protective top layer that provides long lasting wear and outperforms the competition in tear resistance and tensile strength. Designed for use in medium duty dry work areas.

Specifications

Model No	825C0048BY
Color	Black/Yellow
Dimensions	4ft x Specify Length
Thickness	3/8in
UPC	662641729117
Brand	NoTrax
Available Colors	Black; Black/Yellow; Gray
Roll Sizes	3'x60', 4'x60'
Custom Lengths	3' and 4' widths (up to 60' long)
Standard sizes	2'x3', 3'x5', 3'x10'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Electrostatic charge (walking test), meets ISO6356 and EN1815 Free of DOP, free of DMF, free of ozone depleting substances, free of silicone and free of heavy metals Meets IEC61340-4-1 (category DIF), measured resistance $R_g 10^6 - 10^9 \Omega$, $R_p 10^6 - 10^9 \Omega$
Recommended Use	For placement in ESD assembly lines, picking, packing and logistics warehouses, individual work stations.
Special Remarks	With Dyna-Shield® - The only mid-priced/high performance anti-fatigue sponge mat available with durability approaching that of competitive "laminated" mats. Extends service life by 50%.
Edges	Beveled edges on all sides
Usage Intensity	Medium duty
Custom Description	Available in stock and rolls sizes and in custom lengths. Available colors in gray, black/yellow and black.
Cleaning Remark	Sweep regularly or dry mop the surface and the back of the mat. The surface can be damp-mopped with a mild soap/detergent. Use ESD mat cleaner.
Surface Detail	Structured Pebble Pattern
Process	Foaming

Weight Lbs/sqft	0.64
Thickness Inch	3/8in
Fire Rating US	Pass
REACH Compliant	Reach compliant (Registration, Evaluation, Authorization and Restriction of Chemicals).
Anti-Fatigue Rating	Better
Slip Resistance Rating	Better
Wear Resistance Rating	Better