



2' x Custom Length, Black-Yellow, Dura Trax® Grande™ Anti Fatigue Mat, 990

Product Images



Short Description

- Nitrile rubber diamond plate top surface is combined with a dense closed cell PVC foam base
- Made from 100% recycled materials
- Diamond-plate surface texture provides added traction
- Withstands exposure to grinding sparks up to 600°F
- UniFusion™ bond guaranteed for the life of the mat

Description

Dura Trax® Grande™ is a full ONE-INCH thick high performance anti-fatigue floor mat representing the ultimate in comfort and durability for today's industrial environments. A nitrile rubber top surface provides a noticeably softer and more comfortable work surface and a diamond-plate design offers greater slip resistance and is easy to sweep or mop clean. Dura Trax® Grande™ combines the heavy-duty nitrile rubber top surface with a dense sponge backing utilizing Notrax® exclusive UniFusion™ technology. This virtually eliminates the possibility of de-lamination. All Notrax® laminate floor mats come standard with RedStop™, a uniquely engineered non-slip backing technology that eliminates the slipping and sliding of floor mats on smooth surface flooring such as vinyl composite tile, painted or epoxy coated concrete, vinyl sheet flooring, carpet, and ceramic tile. The sloped beveled edges reduce tripping hazards and allow easy access on and off the mat. In addition, the rubber surface of the mat resist exposure to sparks making it the perfect choice for welding applications.

Specifications

Model No	990C0024YB
Color	Black/Yellow
Dimensions	2ft x Specify Length
Thickness	1in
UPC	662641829879
Brand	NoTrax
Roll Sizes	2'x75', 3'x75', 4'x75'
Custom Lengths	2', 3' and 4' widths (up to 75' long)
Standard sizes	2'x3', 3'x5', 3'x12'
Group	Ergonomic, Anti-fatigue & Safety Matting
Environment	Dry Areas
Special Characteristics	Coefficient of friction NSF1 certified
Recommended Use	In manufacturing plants, production lines, assembly lines, CNC machines, metal working, fabrication
Special Remarks	The rubber surface of the mat has a noticeably softer feel and provides greater friction for slip resistant work area and resists exposure to sparks making it the perfect choice for welding applications.
Edges	Beveled edges on all sides
Usage Intensity	Heavy duty
Material Specifications	Nitrile rubber on microcellular vinyl base
Surface Detail	Industrial Diamond Plate
Backing	Closed Cell Polyvinylchloride with RedStop™ slip-resistant backing
Process	Lamination
Weight Lbs/sqft	1.5
Thickness Inch	1in
Fire Rating US	Pass

Anti-Fatigue Rating	Superior
Slip Resistance Rating	Superior
Wear Resistance Rating	Superior

Prop 65

⚠️WARNING: This product can expose you to chemicals including di-2-ethylhexyl phthalate and/or diisononyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.