

Moisture Trap Entry Scraper Mat Finger Scrape[®] T28

Product Images



Short Description

- Tough rubber compound remains flexible while withstanding extreme cold
- Thousands of flexible rubber fingers sweep shoes clean
- Vertical grip lines on the underside of the mat minimize shifting
- Molded beveled edging on all 4 sides creates a retention dam to trap moisture while reducing trip hazards

Description

Finger Scrape® mats are constructed of tough SBR rubber to remain flexible while withstanding extreme cold. Thousands of tough, flexible rubber fingers sweep shoes clean while vertical grip lines on the underside of the mat help to minimize shifting. Due to its durable construction, Finger Scrape® is the perfect year round outdoor entrance mat for schools, municipal buildings, plant entrances, and office buildings.

Specifications

Model No	T28
Available Colors	Black
Overall Thickness	1/4
Standard sizes	32"x 39"
Group	Entrance Matting
Environment	Outdoor
Special Characteristics	Suitable for use in extreme weather
Special Remarks	Be sure to check door clearance
Surface	Flexible Rubber Bristles
Edges	Beveled edges on all sides
Usage Intensity	Medium traffic
Material Specifications	Natural rubber
Process	Compression Molding
Weight Lbs/sqft	1.6
Dirt Scraping Rating	Superior
Outdoor Use Rating	Better
Wearability Rating	Best

Prop 65

⚠️WARNING: This product can expose you to di-2-ethylhexyl phthalate which is known to the State of California to cause cancer, birth defects or reproductive harm. For more information, visit www.P65Warnings.ca.gov.

Product Options

Dimensions:	3ft x 6ft
	24in x 32in
	32in x 39in