115 Standard Duty Loop Hanger

1150500EG

The 115 Standard Duty Loop Hanger, part of the CADDY® line of fasteners and supports from ERICO, is ideal for suspending stationary, non-insulated pipe lines, including CPVC pipes, in fire sprinkler systems. A knurled insert nut helps simplify vertical adjustments and flared edges on the base (1/2” to 4” sizes) help protect pipes from coming into contact with any sharp edges of the hanger.

Features

- Flared edges help prevent any sharp surfaces from coming into contact with the pipe (1/2" to 4" sizes)
- Retained insert nut helps ensure the loop hanger and insert nut stay together
- Recommended for the suspension of stationary non-insulated pipe lines
- Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping
- Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 and SP-69 (Type 10)

Product Specifications

Part Number	1150500EG
Material	Steel
Finish	Pre-galvanized
Pipe Size	5"
Outer Diameter (OD)	5 9/16"
Rod Size (RS)	1/2"
A	9 13/16"
B	4 3/4"
C	2 1/4"
Static Load (F)	1,000 lb
Standard Packaging Quantity	25 pc
UPC	78285636163
UNSPSC	40141725
Approvals	cULus®, FM®