

418 J-Hanger

4180050EG



Features

- Recommended for the suspension of stationary non-insulated pipe lines
- T-slot hole for bolt head permits disengagement of side bolt without removing the nut (sizes 1/2" thru 4" only)
- Side hole permits wall mounting (sizes 1/2" thru 4" only)
- Conforms with Manufacturers Standardization Society (MSS) SP-58 and SP-69 (Type 5)

Product Specifications

Part Number	4180050EG
Material	Steel
Finish	Electro-galvanized
Pipe Size	1/2"
Rod Size (RS)	3/8"
A	2 15/16"
B	1 11/16"
C	1 9/16"
Static Load (F)	400 lb
Standard Packaging Quantity	50 pc
UPC	78285633993
UNSPSC	40141725

