

Spill Decks / Pallets



There's no need to worry about incidental spills on your factory floor. These spill decks are easy to load with a low profile design and optional ramp. Each spill deck is designed for stand-alone use or can connect with other spill decks for using Link-Locks, for a customized work area.

- Tough, one piece polyethylene construction will not rust or corrode.
- Large sump capacity catches incidental spills.
- Removable heavy-duty structural form grates for easy cleaning.
- Rolled-edge design helps resist cracking and warpage.
- Doors include 3-point latching device with key lock.
- Ramp hooks onto spill deck for easy loading.
- Create a solid workspace using Link-Locks.

SPILL DECKS

Part #	Description	Dimensions	Load Capacity lb (kg)	Spill Capacity gal (L)	Weight lb (kg)	Regulations
450512	2 Drum Spill Deck	inch: 53 x 28.5 x 6 cm: 135 x 72 x 15	2400 (1089)	22 (83.2)	39 (18)	EPA 40 CFR 264.175, SPCC, NPDES and UFC
450514	4 Drum Spill Deck	inch: 53 x 53 x 6 cm: 133 x 135 x 15	6000 (2722)	40 (151.4)	71 (32)	EPA 40 CFR 264.175, SPCC, NPDES and UFC
450516	6 Drum Spill Deck	inch: 77 x 53 x 6 cm: 196 x 135 x 15	7000 (3175)	61 (230.9)	102 (46)	EPA 40 CFR 264.175, SPCC, NPDES and UFC
450518	8 Drum Spill Deck	inch: 100 x 53.25 x 6 cm: 254 x 135 x 15	8000 (3629)	77 (291.4)	163 (74)	EPA 40 CFR 264.175, SPCC, NPDES and UFC
450520	Link Lock for Spill Decks, 1 pair	inch: 9.5 x 7 x 3.5 cm: 24 x 18 x 9	—	—	3 (1.3)	—
450555	6" Ramp	inch: 46 x 26 x 6 cm: 117 x 64 x 16	1000 (454)	—	30 (14)	—



Spill pallets offer greater secondary containment to meet regulatory requirements. Raised edges on back and sides helps orient barrels on the pallet. Pallets are forkliftable and have removable grates for easy cleaning. Includes drain and plug.

The IBC Spill Pallet gives bulk container users more versatile spill containment. It fits more than 99% of all IBC dispensing units and features a large sump capacity of 385 gallons; more than exceeding EPA 40 CFR 264.175 regulations. The unit also comes with an integrated 5-gallon pail holder for quick and easy dispensing. A one-piece, light weight, 100% polyethylene IBC spill containment unit that is forkliftable and nestable for convenient shipment and storage and it reduces shipping costs. The polyethylene construction will not rust, corrode, or have adverse reactions with chemicals.

SPILL PALLETS

Part #	Description	Dimensions	Load Capacity lb (kg)	Spill Capacity gal (L)	Weight lb (kg)	Regulations
450612	2 Drum Spill Pallet	inch: 54 x 29 x 17 cm: 136 x 74 x 43	2000 (907)	58 (219.5)	56 (25)	EPA 40 CFR 264.175, SPCC, NPDES
450614-IL	4 Drum - In Line Low Profile Spill Pallet	inch: 98 x 25 x 12 cm: 249 x 64 x 30	3000 (1361)	66 (250)	84 (38)	EPA 40 CFR 264.175, SPCC, NPDES and UFC
450614-LP	4 Drum - Square Low Profile Spill Pallet	inch: 54 x 54 x 12 cm: 137 x 137 x 30	6000 (2721)	66 (250)	91 (42)	EPA 40 CFR 264.175, SPCC, NPDES and UFC
450503	IBC Spill Pallet	inch: 73 x 81 x 30 cm: 185 x 204 x 75	8000 (3629)	385 (1457)	291 (132)	EPA 40 CFR 264.175, SPCC, NPDES and UFC
450315	12" Ramp	inch: 68 x 31 x 12.5 cm: 172 x 78 x 32	1000 (454)	—	65 (30)	—
450316	Ramp Extender	inch: 29.5 x 8.5 x 5.5 cm: 75 x 22 x 14	1000 (454)	—	6 (2.7)	—