

BREATHER ADAPTERS

Adapter Kits are available in dark gray and configured with Colorized Quick Connects* and are available in 10 OilSafe colors or silver, no Quick Connects or Iso-b Quick Connects. Adapter Kits allow breathers to be installed on any storage tank, drum, hydraulic fluid tank, reservoir or gearbox.



DRUM ADAPTER KIT

There's never been a cleaner, more effective way to store, filter and pump lubricants from a drum. The unique design ensures all fluid handling is managed through dedicated adapters.

HYDRAULIC RESERVOIR ADAPTER KIT

The aluminum adapters have quick connects in two sizes - 3/4" suction for pump oil in and 1/2" return for pump oil out for pumping oil in and out, allowing the system to remain closed to the environment at all times.

GEARBOX ADAPTER KIT

Oil can be pumped in or out without opening the gearbox to atmosphere. Offline filtration, and oil changes and sampling can be handled through the adapter.

DOMED FLANGE ADAPTER PART # 095A114DG

Domed Flange Adapters provide a low profile yet rugged way to mount a 1" NPT desiccant breather to a hydraulic reservoir.



Adapter Kit Part # Configuration:

Adapter Styles

Drum Adapter = 960
Hydraulic Reservoir Adapter = 961
Gearbox Adapter = 962

+ Quick Connect Size

12 = 1/2"
34 = 3/4"

+ Quick Connect Color

BG = Beige	PL = Purple
BK = Black	RD = Red
BL = Blue	SL = Silver
DG = Dark Green	YL = Yellow
GY = Gray	ISO = No Color (iso-b)
MG = Mid Green	NQ = No Connect
OR = Orange	

+ Quick Connect Type

(Do not add if NQ picked for Quick Connect Color)

M = Male
MF = Male & Female

(EXAMPLE: 960BGM - Drum Adapter, Beige, Male)

MULTI-THREAD ADAPTER

Allow a breather to be installed easily on various threaded connections. The universal threads allow for a connection with NPT, BSPP, and BSPT thread types.

PART

9631	1"
96312	1/2"
9631238	1/2"-3/8"
963134	1"-3/4"



COLORIZED QUICK CONNECTS

Offer a flexible, durable and safe hose interface for use with lubrication management equipment. Manufactured from anodized aluminum, then color-coded, these connects are specially designed to eliminate cross-contamination once and for all. They are available in 10 familiar OilSafe colors* or silver to easily identify fluid contents and set

1/2" MALE	1/2" FEMALE	3/4" MALE	3/4" FEMALE
PART #	PART #	PART #	PART #
M8 Orange	F8 Orange	M12 Orange	F12 Orange
M8 MidGreen	F8 MidGreen	M12 MidGreen	F12 MidGreen
M8 DrkGreen	F8 DrkGreen	M12 DrkGreen	F12 DrkGreen
M8 Blue	F8 Blue	M12 Blue	F12 Blue
M8 Purple	F8 Purple	M12 Purple	F12 Purple
M8 Red	F8 Red	M12 Red	F12 Red
M8 Beige	F8 Beige	M12 Beige	F12 Beige
M8 Black	F8 Black	M12 Black	F12 Black
M8 Gray	F8 Gray	M12 Gray	F12 Gray
M8 Yellow	F8 Yellow	M12 Yellow	F12 Yellow
M8 Silver	F8 Silver	M12 Silver	F12 Silver

the bar with an error-proof/exclusive fit. Only two terminals of the same color can fully connect making cross-contamination impossible. Our OilSafe Quick Connects keep your machinery and fluids lasting longer while maintaining a safe work environment with precise and secure connections that eliminate leaks, spills and waste. Max Operating Pressure 1,000 psi. Service Temperature 80°C/176°F.

*Colorized quick connects have been inspected to ensure anodized colors are within OilSafe color spectrum scope. Color and shade can vary on anodized components, this will not impact performance of product.