



Complementary Brass Compression Fittings


0124 Brass Olive

	Brass		ØD		kg
			4	0124 04 00	0.001
			5	0124 05 00	0.001
			6	0124 06 00	0.001
			8	0124 08 00	0.001
			10	0124 10 00	0.003
			12	0124 12 00	0.004
			14	0124 14 00	0.005
			15	0124 15 00	0.004
			16	0124 16 00	0.006
			18	0124 18 00	0.007
			20	0124 20 00	0.009
			22	0124 22 00	0.012
			25	0124 25 00	0.017
			28	0124 28 00	0.017

0124..40 Steel Olive

	Zinc-plated steel		ØD		kg
			4	0124 04 00 40	0.001
			6	0124 06 00 40	0.001
			8	0124 08 00 40	0.001
			10	0124 10 00 40	0.003
			12	0124 12 00 40	0.003
			14	0124 14 00 40	0.005
			15	0124 15 00 40	0.004
			16	0124 16 00 40	0.006
			18	0124 18 00 40	0.007
			20	0124 20 00 40	0.007
			22	0124 22 00 40	0.010
			25	0124 25 00 40	0.014

0111 BNA* Brass Olive

	Brass		ØD		kg
			4	0111 04 00	0.001
			5	0111 05 00	0.001
			6	0111 06 00	0.001
			8	0111 08 00	0.001
			10	0111 10 00	0.002
			12	0111 12 00	0.002
			14	0111 14 00	0.003
			15	0111 15 00	0.003
			16	0111 16 00	0.003

*BNA: Bureau de Normalisation de l'Automobile (standards organization in the field of Automotive Process)