



Over One Million
Cycle Tested

CE Marked

Limited Lifetime
Warranty

Compliant

EDGEHALT™ ADJUSTABLE SAFETY GATE

A SINGLE GATE SIZE FOR OPENINGS 18" – 36"

Our new self-closing EdgeHalt™ Adjustable Safety Gate makes it easy to protect your team from the dangers of an elevated guardrail opening. This one gate is flexible enough to fit a large range of openings, reducing the need to measure every opening within your facility. Plus, it's stocked and ready to ship within three days!*

ONE GATE SIZE:

- Adjustable to fit openings from 18" to 36" (457mm – 914mm), and inverts to swing left or right

GUARANTEED-FOR-LIFE SPRINGS:

- Designed and tested to withstand over 1 million cycles

EASY INSTALLATION:

- No sawing or cutting required

CODE COMPLIANT:

- CE marked, meets OSHA, ANSI, Canada OHS and CSA guardrail standards

FINISH:


- Mild steel, safety yellow powder coat

ALWAYS IN PLACE:

- Self-closing to protect employees from dangerous falls

MOUNTING OPTIONS:

- Standard railing mount (shown to the right)
- Flat surface mount (shown below) changes gate range to 20.5" – 38.5" (521mm – 978mm)



Product Number: ASG-1836-PCY

**PATENT
PENDING**

EdgeHalt™ Adjustable Safety Gate Options



Stand-Off
Mounting System



GrabSafe®

*Larger quantities and international orders may require longer lead times