



1 in. Flex Straight Squeeze Connector, Uninsulated

By RACO
Catalog # [2104](#)

1 in. Flex Straight Squeeze Connector, Uninsulated



Features

- All malleable construction ensures mechanical protection for the raceway
- Electro zinc plated for added corrosion protection
- UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

Specifications

Certified Listed cULus Listed

Configuration

Connector Type Squeeze

Dimensions

Length 1.688 in
Trade Size 1 in
Weight 0.313 lb.
Height 2.391 in

Width 1.72 in
Dimensions 1.688 in x 1.72 in x 2.391 in

General

Conduit Type Flexible Metal Conduit
Product Family Flexible Metal
Fitting Type Connectors
Product Type Commercial Fittings
UPC 050169021040
Material Malleable Iron

Logistics

Minimum Pack Quantity 25
Pallet Quantity 7500
Carton Quantity 25

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)