



1-Gang Masonry Box, Gangable, 2-1/2 in. Deep, Eight TKO's

By RACO
Catalog # 688

1-Gang Masonry Box, Gangable, 2-1/2 in. Deep, Eight TKO's



Features

- Rugged welded design does not fall apart during construction.
- Gangable design allows installer to build unlimited number of gangs to hold multiple devices.
- Rectangular shape fits square cuts in block.
- Standard 1/2" and 3/4" TKO knockouts.
- Device ears inside the box prevent mortar from getting in the device holes.
- Steel voltage partition #675 fits 2-1/2" and #676 fits 3-1/2" depth.
- Forward mounted grounding provision allows for easy installation of grounding pigtail.
- Standard wall plates can be used.
- Supplied with eight (8) 1/2 & 3/4 in. concentric knockouts
- Gangable design allows construction of multiple gang box from one product
- Ground is located near the front of the box for installer's convenience
- 15.5 cu. in. capacity
- For 4 in. block walls

Specifications

Certified Listed UL Listed

Configuration

Gangable	Yes
Number of Gang(s)	1-Gang
Knockouts	1/2 in - 3/4 in Combination (TKO)
Bracket Type	No Bracket

Dimensions

Cubic Capacity	15.5 cu.in
Depth	2.5 in
Weight	0.635 lb.
Height	3.875 in
Width	2.21 in

General

Color	Gray
Product Family	Masonry Boxes & Supports
Wiring System	Conduit
Product Type	Steel Boxes and Covers
UPC	050169006887
Type	Box
Material	Steel

Logistics

Pallet Quantity	2000
Carton Quantity	20
Packaging Type	No Packaging

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)