



3-1/2 in. Round Ceiling Pan, Drawn, 1/2 in. Deep, One 1/2 in. KO and NMSC Clamps

By RACO
Catalog # 8292



3-1/2 in. Round Ceiling Pan, Drawn, 1/2 in. Deep, One 1/2 in. KO and NMSC Clamps

Features

- Rated for 50 lb. fixture support
- Combination screw heads provide for faster installation
- L clamps provided for Nonmetallic Sheathed Cable (NMSC)
- Supplied with one 1/2 in. knockout
- 6.0 cu. in. capacity
- Do not use to support ceiling fans

Specifications

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
EU RoHS Indicator	Contact Manufacturer
Description SPEC - Certification	• Canada 1,324,360 • Mexico 166,125.
Buy America(n) Qualified	Contact Manufacturer

Configuration

Knockouts	1/2 in
-----------	--------

Current

Power Distribution Features	Fire Rated
-----------------------------	------------

Dimensions

Cubic Capacity	4.0 cu.in
Fixture Lbs.	50 lb.
Depth	0.5 in

Weight	0.286 lb.
Height	3.375 in
Width	3.375 in
Actual Depth	0.578 in
Size	3.5 in
Raised Ground	No

General

Color	Gray
Ceiling Fan Rated	No
Wiring System	Nonmetallic Sheathed Cable
Drawn or Welded	Drawn
UPC	050169002926
Type	Ceiling Pan
Material	Steel

Logistics

Pallet Quantity	4200
Carton Quantity	25
Packaging Type	No Packaging

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)