



4-11/16 in. Square Work, Exposed Work, 30-50A Receptacle 2.141 in. Dia

By RACO
Catalog # 878

4-11/16 in. Square Work, Exposed Work, 30-50A Receptacle 2.141 in. Dia

Features

- Galvanized steel construction
- 30-50A receptacle, 2.141" dia.
- Includes required hardware for mounting the receptacle(s)
- UL Listed

Specifications

Certified Listed cULus Listed

Dimensions

Length	0.563 in
Cubic Capacity	10.3 cu.in
Weight	0.479 lb.
Height	4.69 in
Width	4.69 in
Size	4-11/16 in
Dimensions	0.563 in x 4.69 in x 4.69 in

General



Color	Gray
Product Family	4-11/16 in. Square Exposed Work/Surface Covers
Product Type	Cover
UPC	050169008782
Type	Exposed Cover
Material	Steel
Paintable/Stainable	Yes

Logistics

Minimum Pack Quantity	10
Pallet Quantity	2880
Carton Quantity	10
Packaging Type	Polybag

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)