

## Spring Retractable Hose Reels



**Water** - 1/2", 5/8", 3/4" I.D.

- Most models include outlet hose with brass on/off ball valve, bumper, and inlet hose providing a reel solution out of the box
- Comes equipped with garden hose end fittings
- Guide arm is easily adjustable to numerous positions
- All steel parts are individually powder-coated for maximum corrosion resistance
- Designed to be mounted centrally and used for watering and washdown
- Reel components are made from industrial-grade steel



GCD83075 OLP



**Interactive Reel Catalog**

Visit [reelcraft.com/catalog](http://reelcraft.com/catalog) for complete product specifications, parts, and accessories.



**Pivot Bases & Swing Brackets**  
See page 39



**Hose Assemblies & Bumper Stops**  
See pages 36-37

Model with hose & bumper	Shipping Weight		Hose I.D.		Hose O.D.		Hose Length		Pressure		GH(M) Hose Outlet in	GH(F) Reel Inlet in	Inlet Hose (included)	Size Index Page	Size Index #
	lbs	kg	in	mm	in	mm	ft	m	psi	bar					
<b>Low Pressure Air/Water Reels</b> Maximum temperature 150°F (65°C)															
7850 OLPSW57	51	24	1/2	13	.810	21	50*	15	150	21	3/4	1/2 NPT	-----	12	----
GC82075 OLP	88	40	1/2	75	.750	19	75	23	150	18	3/4	3/4	S601025-8	14	1
GC7535 OLP	53	24	5/8	16	1.00	26	35	11	150	18	3/4	3/4	S600830-10	12	----
GCD85100 OLP	101	46	5/8	16	1.00	26	100	31	150	18	3/4	3/4	S600830-10	14	2
GC83050 OLP	89	41	3/4	19	1.075	27	50	15	150	18	3/4	3/4	S600830-10	14	1
GCD83075 OLP	102	46	3/4	19	1.075	27	75	23	150	18	3/4	3/4	S600830-10	14	2

\*50 ft. hose assembly is yellow; does not include ball valve or inlet hose.

## Portable Hose Reel and Cart



**Water** - 1/2", 1" I.D.

- Series 30000 reels mounted on a portable cart are designed for rugged, heavy-duty applications requiring long lengths of hose and large storage capacity



600965

### Additional Hoses

1" ID x 100', 1" NPT x 1" NPSH: **S600982-100**

3/4" ID x 150', 3/4" NPT x 1" NPSH: **S601044-150**

1" ID x 10', 1" NPT x 1" NPSH: **S600982-10**

### Garden Fitting Conversion Kits

1/2" NPTM x 3/4" GH: **S260729**

3/4" NPTM x 3/4" GH: **S261702**

Hose Reel and Cart Packages	
Package	Items Included
<b>600966</b>	1/2" x 200' hand crank hose reel (CA32112 L); 12" hand cart with semi-pneumatic tires (600741-2); 5/8" x 10' PVC inlet hose (600962)
<b>600968</b>	1" x 100' hand crank hose reel (CH37118 L); 18" hand cart with semi-pneumatic tires (600885-2); 1" x 10' PVC inlet hose (S600982-10)

Refer to page 25 for Series 30000 hose reel dimensions and specifications.

	600741-2		600885-2	
	Reel Size		Reel Size	
	in	mm	in	mm
<b>A</b>	Adjustable*			
<b>B</b>	23 3/4	603	28 3/4	730
<b>C</b>	18 1/4	464	18 1/4	464

\*Handle height of cart is adjustable to 35 5/8", 38 5/8", 41 1/2" or 44 1/2". Eight 5/16" (8mm) diameter mounting holes.