

Eye bolt RS-9/16"-12UNC

Artikel-Nr: 57120




- **Considerably higher WLL**(in comparison to DIN 580/582) at vertical load.
- **Large thread and WLL range** (M6-M48, 0.1 t – 8 t).
- **Clear marking of the minimum WLL for all loading directions**
- Quick and easy installation with just one bolt connection.
- In accordance with the test principles of DGUV GS-HM-36, eyebolts with rigid eyes serve as mounting aids, e.g. on motors and gear units. There is a trade association clearance certificate available for using the high-strength RUD RS eyebolts.

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

Eye bolt RS-9/16"-12UNC

Artikel-Nr: 57120



weight	0.30 kg	0.66 lbs
Nominal WLL	750 kg	1650 lbs
T	48 mm	1-7/8"
A	22 mm	7/8"
B	15 mm	19/32"
C	14 mm	9/16"
D	35 mm	1-3/8"
E	35 mm	1-3/8"
M	9/16"-12UNC mm	9/16"-12UNC