

## STARPOINT VRS-0,75t-M14

Artikel-Nr: 7100557



- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Variable bolt lengths available for tapped or through holes.
- Available as: – Standard Metric Thread (DIN EN 13) – Metric Fine Thread (DIN EN 13) – Coarse Pitch Thread UNC (ANSI B1.1) – Fine Thread 8UN (ANSI B1.1) – Inch Pipe Thread (DIN 228)
- Significant product characteristics of the VRS are subject to property right claims.
- Tested and certified by DGUV. Testing specifications: GS-HM-36: 2023-06, Certificate No.: HM 250037
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- Installation and disassembly without any further tools than the exchangeable Easy-Fit star profile key for singular lifts (Version VRS-F).
- For permanent installation and recurrent lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

STARPOINT VRS-0,75t-M14

Artikel-Nr: 7100557



|             |         |          |
|-------------|---------|----------|
| weight      | 0.20 kg | 0.44 lbs |
| Nominal WLL | 750 kg  | 1650 lbs |
| T           | 42 mm   | 1-21/32" |
| B           | 13 mm   | 1/2"     |
| C           | 10 mm   | 3/8"     |
| D           | 30 mm   | 1-3/16"  |
| E           | 30 mm   | 1-3/16"  |
| G           | 34 mm   | 1-11/32" |
| I           | 19,8 mm | 25/32"   |
| K           | 56 mm   | 2-3/16"  |
| L           | 18 mm   | 23/32"   |
| M           | M14 mm  | M14      |
| N           | 8 mm    | 5/16"    |