

## STARPOINT VRS-3,2t-1"-8UNC

Artikel-Nr: 7103964




- Lifting points pivots 360°. Easy adjustment in load direction.
- Not exchangeable RUD-Bolt (this reduces the usage of improper standard bolts).
- Clear marking of the minimum WLL for all loading directions. Higher WLL possible when location and installation is optimised (compare WLL chart / product information).
- Clear marking at the bolt head: RUD, thread size, batch-no.
- Variable bolt lengths available for tapped or through holes.
- Available as: - Standard Metric Thread (DIN EN 13) - Metric Fine Thread (DIN EN 13) - Coarse Pitch Thread UNC (ANSI B1.1) - Fine Thread 8UN (ANSI B1.1) - Inch Pipe Thread (DIN 228)
- Significant product characteristics of the VRS are subject to property right claims.
- Component according to the test criterias of BG/DGUV "GS-HM 36".
- Complying with the US-Standard (ASME B30.26). Quick and easy installation with just one bolt connection.
- Installation and disassembly without any further tools than the exchangeable Easy-Fit star profile key for singular lifts Version VRS-F).
- For permanent installation and recurrent lifts we can offer a special socket wrench to apply the requested torque (fits to a common Inch torque wrench).

Other important RUD specific information and specialities to our RUD lifting points can be found in the specific user instruction.

## STARPOINT VRS-3,2t-1"-8UNC

Artikel-Nr: 7103964



<b>weight</b>	0.90 kg	1.98 lbs
<b>Nominal WLL</b>	3200 kg	7050 lbs
<b>T</b>	70 mm	2-3/4"
<b>B</b>	20 mm	3/4"
<b>C</b>	19 mm	3/4"
<b>D</b>	49 mm	1-15/16"
<b>E</b>	51 mm	2"
<b>G</b>	60 mm	2-3/8"
<b>I</b>	35 mm	1-3/8"
<b>K</b>	92 mm	3-5/8"
<b>L</b>	36 mm	1-27/64"
<b>M</b>	1"-8UNC mm	1"-8UNC
<b>N</b>	9/16" mm	9/16"